

Datasheet

Time-Lag Ceramic Tube Fuse With Pig-Tail

3.6ØX10mm



Number	Ampere Rating (in)	Voltage Rating (V)	Nominal Resistance Cold Ohms	Voltage Drop (mv) Max.	Nominal Melting I ² t A ² Sec
911-3512	250mA	250V	0.7310	240	0.3262
911-3521	315mA		0.4720	220	0.5255
911-3524	400mA		0.3160	200	0.7296
911-3528	500mA		0.2560	190	1.3100
911-3537	630mA		0.1700	180	2.6179
911-3530	800mA		0.1130	160	4.0645
911-3534	1A		0.0860	140	6.6388
911-3543	1.25A		0.0640	130	14.738
911-3546	1.6A		0.0460	120	29.768
911-3540	2A		0.0340	100	32.976
911-3559	2.5A		0.0260	100	61.200
911-3552	3.15A		0.0190	100	91.197
911-3556	4A		0.0140	100	149.98
911-3565	5A		0.0100	100	188.60
911-3568	6.3A		0.0080	100	27676

Electrical Characteristics

Rated Current	1.5 in		2.1 in		2.75 in		4 in		10 in	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
250mA ~ 6.3A	60 min	2 min	400 ms	10 sec	150 ms	3 sec	20 ms	150 ms		

Interrupting Rating

35 amperes or 10 x rated current; whichever is greater at 250V ac

Operating Temperature

-55°C to +125°C

Physical Specification

Material

Ceramic body / Nickel Plated Brass Caps

Lead Wire: Diameter 0.6 mm, 4A and Less
Diameter 0.8 mm, 5A and 6.3A

Dimensions

