








1		2		3		4		5		6		7		8			
△BMSDS-XXBFFA-SL7001 XX: No. Of Pin				REV.	ECN NO.	DATE	SIGN	DESCRIPTION									
				C	C210084	2021/01/18	Vicky	△C X3									
				D	C210561	2021/04/19	Vicky	△D X2									
				E	C221877	2022/12/13	Ruru	△E X1									
      Connector Clamp Ring O-Ring Clamp Cage Seal Sealing Nut																	
  16.0 Hex. 16.0 Hex.																	
 4P Pin Assignments Front View																	
UNIT:mm						TITLE N SEN, M12 D -SHLD, SCREW CABLE W/O SR, F, F, FI SOLDER				ITEM NO		DRAWN BY JC Chen		DATE 2020-04-18			
TOLERANCE		±0.25		±0.1		SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG. NO △BMSDS-XXBFFA-SL7001		CHECKED BY Li Feng		DATE 2020-04-18	
.X		±0.25		±0.1		REV. E		WC-REV. A.5		QC:Inspection item		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2020-04-18	
.XX		±0.1		±0.05													
.XXX		±0.05		±1°													
ANGLES		±1°															

△D
Note:

- * RoHS Compliant
- * Ⓞ Important Dimension
- △E * Waterproof rate: IP67, mated
- * Connector
- Housing: Thermoplastic, Black
- Pin: Copper alloy, Gold plated
- Extension Nut: Metal
- △C * Nut: Metal
- O-Ring: Rubber, Gray
- △C * Clamp Ring: Metal
- * O-Ring: Rubber, Gray
- * Clamp Cage: Thermoplastic, Black
- △C * Sealing Nut: Metal
- * Seal: Rubber, Gray, OD:Ø4.0mm~Ø7.5mm
- * One set un assembled in one pe bag

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.