

# AI 50-25 OL - Ferrule

2100023

<https://www.phoenixcontact.com/gb/products/2100023>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 25 mm, sleeve length: 40 mm, color: olive

## Your advantages

- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- In terms of dimensions, they correspond to DIN 46228-4: 1990-09

## Commercial data

Item number	2100023
Packing unit	25 pc
Minimum order quantity	10,000 pc
Sales key	BH3411
Product key	BH3411
GTIN	4067923214262
Weight per piece (including packing)	3.42 g
Weight per piece (excluding packing)	3.42 g
Customs tariff number	85369010
Country of origin	DE

# AI 50-25 OL - Ferrule

2100023

<https://www.phoenixcontact.com/gb/products/2100023>



## Technical data

### Product properties


Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-1 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

### Connection data

#### Conductor connection

Conductor cross section flexible max.	50 mm <sup>2</sup>
Conductor cross section AWG max.	1/0
Stripping length	30 mm

### Dimensions

Dimensional drawing	
Sleeve length	40 mm
Length contact range	25 mm
Maximum stripping length	30 mm
Ferrule diameter	10.3 mm
Sleeve wall thickness	0.35 mm
Insulating collar thickness	0.6 mm
Inner dimensions of the insulating collar	15 mm

### Material specifications

Color	bottle green (RAL 6007)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

#### Technical data

# AI 50-25 OL - Ferrule



2100023

<https://www.phoenixcontact.com/gb/products/2100023>

Sleeve length	40 mm
---------------	-------

## Standards and regulations

Design according to standard	Special color
------------------------------	---------------

## Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

# AI 50-25 OL - Ferrule

2100023

<https://www.phoenixcontact.com/gb/products/2100023>



## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2100023>



**cULus Listed**

Approval ID: E488001

# AI 50-25 OL - Ferrule



2100023

<https://www.phoenixcontact.com/gb/products/2100023>

## Classifications

### ECLASS

ECLASS-13.0	27400201
-------------	----------

### ETIM

ETIM 9.0	EC000005
----------	----------

# AI 50-25 OL - Ferrule

2100023

<https://www.phoenixcontact.com/gb/products/2100023>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)