

## Features

- Versatile switch suitable for many heavy duty applications
- Compatible with all industry standard V3 switches.
- Available with solder, quick connect and screw terminals.
- Long mechanical and electrical life
- Fire Silver contacts.
- Temperature range upto 85°C
- Positive snap action.
- Conform to IEC 1058-1-standard

## RS PRO Micro Switch

RS Stock No.: 0241246



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Reverse-configured motor variant tailored for specialized applications requiring backward operation

## General Specification

Actuator Type	Long Roller Lever type
Terminal Type	Quick 4.75X0.5
Contact Current Rating	16 AMP
Contact Configuration	Solder Type
IP Rating	40
Operating Force	125 Gms
Minimum Operating Temperature	-55°C
Maximum Operating Temperature	85°C
Switch Housing	G.F PBT
Contact Material	COPPER ALLOY
Case Material	G.F PBT
Mechanical Life	100000
Voltage Rating	250V
Release Force	14 Gms
Switch Operation	Snap Action

<b>Standards Met</b>	CE AND CSA
<b>Applications</b>	Business and office machines Industrial Electronics Defence Power Sector

