

FEATURES

- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight.
- **High Tensile Strength:** Supports up to 55 kg, ensuring robust cable bundling.
- **Wide Temperature Range:** Operates between -40 °C and 85 °C, suitable for various environments.
- **RoHS Compliant:** Meets safety and environmental standards.
- **UL 94HB Rated:** Provides a standard level of flame retardancy.

RS PRO Nylon Cable Tie, 450mm Non-Releaseable

RS Stock No: 656-102



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO nylon cable ties are designed for secure and reliable bundling of cables and wires. With a length of 450mm, they are ideal for managing larger cable bundles, ensuring neat and organised installations. The non-releasable design provides a permanent solution for cable management, making them suitable for long-term applications.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	55 kg

Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

Mechanical Specifications

Length	450 mm
Material	Nylon
Maximum Bundle Diameter	128 mm
Width	8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------