

1100-1.04

Universal puller set

in L-BOXX® 136 13 pieces

Code	ETIM
2838362	EC011834
EAN	UNSPSC
4010886939406	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-90-90
Customs tariff number	
82055980	



Article description

- With 2- and 3-arm cross-beam
- With rigid and slim legs and extensions
- Extra slim Pulling hooks for narrow installation spaces are included for self-installation
- The forged hooked feet are particularly suitable for difficult-to-access places
- 12 different pullers can be combined
- Outside Ø up to 130 mm, inside Ø up to 170 mm with a clamping depth of 200 mm
- With check tool insert for quick identification of missing tools
- No. 1100 CT2-1.04 for retrofitting existing L-BOXX®s 136

Article parts list

Universal puller HIGH POWER No. 1.04/HP1A-B, 2-arm, 130x100 mm ,Crossbeam No. 107/1A03, 3-arm 180 mm ,Pulling leg No. 106/A-100-B, all-steel, leg brake ,3x extension No. 106/A-100-VB with leg brake 100 mm ,3x pulling leg No. 106/A-100-5, slim 100 mm ,3x pulling leg No. 106/S101-5, without clamping part ,Spindle No. 1.1406200, 17 M14x1,5 200 mm ,+ GEDORE L-BOXX® 136 No. 1100 L

Article information

Contents (Qty of pieces)	13	Anti-slip device on the spindle	no
Graduation	no	Exchangeable spindle tip	no
reversible arms available	no	Can be retrofitted with hydraulic spindle	no
Net weight [kg]	6,3 kg	Total length [mm]	444 mm
Hook brake available	no	Total width [mm]	360 mm
Hook can be moved parallel	no	Total height [mm]	152 mm
Quick release lever available	no		