

Features

- Conforms to ANSI/TIA-568.2-D & ISO/IEC 11801-1
- HDPE Insulation
- Mylar & AL-Mylar Tape Construction
- Backwards Compatible to CAT 3 & CAT 5
- Operation Temp -20c - 60c
- Conductor DC Resistance $\leq 140 \Omega$ /1000m

RS PRO Ethernet Cable

RS Stock No.: 0199200



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Combines premium features with VLZ technology for enhanced clarity. The RS Pro Unterminated Cat5e type cables have primary application use for both home and office computer networks. This cable is compliance with CE, UKCA, RoHS, and REACH standards. It features an IP67 rating, ensuring it is protected against dust and water immersion. It has 8 core strands made from LSZH, providing reliable fire behaviour. With stranded conductor strand type and a 26 American Wire Gauge (AWG) it is optimized for applications that demand durability and performance.

General Specification

LAN Category	Cat5e
Length	305m
Terminated/Unterminated	Unterminated
Shield Type	F/UTP
Shielded/Unshielded	Shielded
Coding	T568B
Sheath Colour	Violet
Outer Sheath Material	LSZH
IP Rating	IP67
Core Strands	8
Fire Behaviour	LSZH
Voltage Rating	300V
Conductor Strand Type	Stranded
American Wire Gauge	26AWG
Cable Shape	Round

Number of Strands	8
Outer Diameter (mm)	5.6mm
Cross Sectional Area (mm)	0.1303mm
Current Rating (A)	2.2A
Applications	Cat5e type cables have primary application use for both home and office computer networks