

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Polisher

PRO GPO 14 CE



Convenient handling, fast work progress, and best results

The most important data

Rated input power	1,400 W
No-load speed	750 – 3,000 rpm
Cup wheel, diameter	180 mm

Part Number 0 601 389 060

Technical data

Technical data

Rated input power	1,400 W
No-load speed	750 – 3,000 rpm
Power output	800 W
Grinding spindle thread	M14
Rubber sanding plate, diameter	180 mm
Wire cup brush, diameter	100 mm
Cup wheel, diameter	180 mm
Polishing sponge, diameter	160 mm
Surface brush, diameter	175 mm
Weight	2.5 kg
Packaging dimensions (width x length x height)	200 x 500 x 130 mm
Voltage, electrical	110 V

Noise/vibration information

Polishing

Vibration emission value ah	6 m/s ²
Uncertainty K	1.5 m/s ²



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Ergonomic handle with soft grip and a low weight of only 2.5 kg make it comfortable to operate during work
- Powerful 1,400 W motor with soft start enables continuous work on large surfaces
- Speed selection is ideal for polishing various materials

**HEAVY
DUTY**



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

