


### Main

Range compatibility	PowerPacT PowerPacT B
Product or component type	Cable connector
Device short name	connectors
Accessory / separate part type	Connection accessories
Poles description	1P

### Complementary

Quantity per set	Set of 1
Location of connection	Upstream Downstream
[In] rated current	15...125 A for copper 15...100 A for aluminium
Conductor material	Steel
Connections - terminals	Screw terminal - 1 cable(s) 2.5...95 mm <sup>2</sup> (AWG 14...AWG 3/0) - solid Screw terminal 2.5...95 mm <sup>2</sup> (AWG 14...AWG 3/0) - stranded Screw terminal 2.5...70 mm <sup>2</sup> (AWG 6...AWG 2/0) - fine stranded

### Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 Yes
PVC free	Yes
Halogen content performance	Halogen free product

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.