



109-23-4
1/4" Socket & Bit Set, 23 Pcs



PRODUCT DETAILS

- 1/4" socket and bit set, 23 pcs
- Hex sockets, metric
- Bright chrome plated finish
- DIN 3120 and DIN 3124
- Ratchet torque according to DIN 3122
- Special ratchet hex 1/4" drive. Reversible. 60 teeth. Length 90 mm
- Bimaterial ratchet handle
- ABS plastic box. Includes belt clip.
- Ratchet sold as a spare part: SP121



PRODUCT ATTRIBUTES

Product			
109-23-4	23	45 x 75 x 110 mm	340 g

SET CONTENT



Socket 1/4" Hex 6 mm
101-06-1



Socket 1/4" Hex 7 mm
101-07-1



Socket 1/4" Hex 8 mm
101-08-1



Socket 1/4" Hex 10 mm
101-10-1



Socket 1/4" Hex 11 mm
101-11-1



Socket 1/4" Hex 13 mm
101-13-1



1/4" Bit Hex 3, 25 mm, Box 5 Pcs
475-H3-1



1/4" Bit Hex 4, 25 mm, Box 5 Pcs
475-H4-1



1/4" Bit Hex 5, 25 mm, Box 5 Pcs
475-H5-1



1/4" Bit Hex 6, 25 mm, Box 5 Pcs
475-H6-1



1/4" Bit PH1, 25 mm, Box 10 Pcs
475-PH1-1



1/4" Bit PH2, 25 mm, Box 10 Pcs
475-PH2-1



1/4" Bit PZ1, 25 mm, Box 10 Pcs
475-PZ1-1



1/4" Bit PZ2, 25 mm, Box 10 Pcs
475-PZ2-1



1/4" Bit T10, 25 mm, Box 10 Pcs
475-T10-1



1/4" Bit T15, 25 mm, Box 10 Pcs
475-T15-1



1/4" Bit T20, 25 mm, Box 10 Pcs
475-T20-1



1/4" Bit T25, 25 mm, Box 10 Pcs
475-T25-1



1/4" Bit T30, 25 mm, Box 5 Pcs
475-T30-1



1/4" Bit Slotted 4.0, 25 mm, Box 10 Pcs
475-4-1



1/4" Bit Slotted 6, 25 mm, Box 10 Pcs
475-6.0-1



1/4" Socket Adaptor, 25 mm
475A-25-1