

# Pro-Lite™ Helix Electronic Compact Fluorescent Lamps

## Electronic Compact Fluorescent Helix Lamps 8000hrs

An electronically ballasted spiral compact fluorescent lamp for use as a direct replacement for GLS mains voltage, and as a creative solution in new installations where energy consumption is important. The 18w version also comes in 3 different colours: Blue, Red and Green.

### Applications

- Ideally suitable for domestic and commercial applications.
- Direct replacement for conventional GLS or 45mm candle lamps.
- In environments that are inaccessible and that require long life lamps to reduce maintenance costs.
- To reduce energy consumption in constantly illuminated areas or where there is a limited power supply.
- Colour Temperature of Lamp 2700



ORDER CODE	Watts	Cap/Base	Length (mm)
HELIX/11W/BC	11w	BC/B22d	101
HELIX/11W/ES	11w	ES/E27	101
HELIX/15W/BC	15w	BC/B22d	108
HELIX/15W/ES	15w	ES/E27	108
HELIX/18W/BC	18w	BC/B22d	113
HELIX/18W/ES	18w	ES/E27	113
HELIX/25W/BC	25w	BC/B22d	140
HELIX/25W/ES	25w	ES/E27	140
HELIX/30W/BC	30w	BC/B22d	162
HELIX/30W/ES	30w	ES/E27	162



## Electronic compact fluorescent coloured Helix lamps 8000hrs

Selected from the extensive range of Pro-Lite Helix lamps, two wattages of the lamp are offered for decorative and effective lighting. 18w or 25w with retro-fit ES and BC bases. Colour is generated through the use of a mix of coloured phosphors inside the spiral tube. This maximises the efficiency (lumen/watt) as no filter or casing is used to create the colour.

ORDER CODE	Watts	Cap/Base	Length (mm)
HELIX/18W/ES BLUE	18w	ES/E27	113
HELIX/18W/BC BLUE	18w	BC/B22d	113
HELIX/18W/ES RED	18w	ES/E27	113
HELIX/18W/BC RED	18w	BC/B22d	113
HELIX/18W/ES GREEN	18w	ES/E27	113
HELIX/18W/BC GREEN	18w	BC/B22d	113



Colours shown are illustrative  
Actual products are not coloured

Ritelite (Systems) Ltd  
Meadow Park, Bourne Road  
Essendine, Stamford, Lincs, PE9 4LT  
Tel : 01780 765600 - Fax: 01780 765700  
E-Mail: [sales@ritelite.co.uk](mailto:sales@ritelite.co.uk)