
PHE F60FTBFLG



Size	60
Bushing no.	1610
Nominal torque (Nm)	-
Nominal torque (lbft)	-
Max torque (Nm)	-
Max torque (lbft)	-
Max speed (r/min)	-
Min. bore (mm)	14
Min. bore (in)	0.55
Max. bore (mm)	42
Max. bore (in)	1.65
Weight (kg)	0.00052
Weight (lbs)	0
E (mm)	25
E (in)	0.98



[®] SKF is a registered trademark of the SKF Group

[©] SKF Group 2012

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.