



# 739-8436 Data Sheet

ENGLISH

Model number : 739-8436  
Type of tool : Die Grinder  
Weight of tool : 0.34 kg

Power Source : Compressed air  
Maximum permissible operating pressure : 90 psi ( 6.2 bar )  
Recommended operating pressure : 90 psi ( 6.2 bar )

### Features

- Allows the operator to reach into very small areas
- Safety lever prevents any possible accidents
- Rear exhaust to keep airflow away from the hand
- High power motor designed for all tight grinding situations

### Specifications

- Size: 6mm Collet
- Free Speed: 25,000RPM
- Weight: 0.34kgs / 0.75lbs
- Length: 4.92" / 125mm
- Min Hose Size: 4.8mm
- Air inlet thread: 1/4"
- Sound: 81dBA
- Vibration: 4m/s<sup>2</sup>
- Ave Air Consumption: 1.68cfm / 47.6 l/min
- Recommended lubrications: 10 Weight SAE Oil

## 739-8436

### Mini Straight Die Grinder

### Technical Data



### Declaration of Conformity

We	RS Components Ltd,
declare under our sole responsibility that the	739-8436 – Mini Straight Die Grinder
conforms with the directive and the standards	2006/42/EEC EN 792-6 ISO 28927