



- Enhance your outdoor space with our sleek and modern twin wall light, featuring a stylish black powder-coated finish. Built to withstand the elements with an IP54 rating, this durable fixture is compatible with LED GU10 and SylSmart colour-changing lamps (not included), offering versatile lighting options. With a long 30,000-hour lifetime and a 3-year warranty, it's the perfect blend of style, performance, and reliability

Product name	YOURHOME SYLWALL UPDOWN
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Wall surface mounted
Light source included	Fixture without Lightsource
General application	Residential & Consumer
ETIM Class	EC002892
Fixture luminous flux (lm)	1
Luminaire efficacy (lm/W)	1
Light colour	N/A
Colour Variation Initial (SDCM)	N/A
Photobiological Risk Group	Not applicable
Total power consumption (W)	1
Electrical protection	Class II
Control gear type	Not required

YOURHOME SYLWALL UPDOWN
0090193

Dimmable	No
Housing colour	RAL9005
IP rating	IP54
IK rating	IK04
Product EAN number	5410288901930
Warranty	3 years
Dimming method	N/A

Data table

GENERAL DATA

Product name	YOURHOME SYLWALL UPDOWN
Technology	LED
Cap/Base	GU10
Housing	Aluminium
Mount	Wall surface mounted
General application	Residential & Consumer
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	3 years

OPTICAL DATA

Fixture luminous flux (lm)	1
Luminaire efficacy (lm/W)	1
Light colour	N/A
Colour Variation Initial (SDCM)	N/A
Distribution type	None
Photobiological Risk Group	Not applicable

ELECTRICAL DATA

Light source included	Fixture without Lightsource
Total power consumption (W)	1

YOURHOME SYLWALL UPDOWN 0090193

Primary Supply/Product voltage - min (V)	220.0
Primary Supply/Product voltage - max (V)	240.0
THD (at 230 V, 50 Hz, full load, at 100% dimming level) \leq xx.x %	1
Electrical protection	Class II
Control gear required	Yes
Control gear type	Not required
Dimmable	No
Dimming method	N/A
Nominal Frequency (Hz)	N/A
Max. products per 10A C Breaker	1
Max. products per 16A C Breaker	1
Max. products per 16A B Breaker	1
Connectable conductor cross section - Max (mm ²)	1.5

PHYSICAL DATA

Housing colour	RAL9005
IP rating	IP54
IK rating	IK04
Diffuser finish	Other
Diffuser material	None
Nominal Product Length (mm)	108
Nominal Product Width (mm)	60
Nominal Product Height (mm)	170
Weight (kg)	0.37

PACKAGING

Product EAN number	5410288901930
Packaging single length / height (cm)	18.0
Packaging single width (cm)	12.0
Packaging single depth (cm)	7.0
DUN14 (inner)	15410288901937
Units per outer package	16



YOURHOME SYLWALL UPDOWN
0090193

Packaging outer length / height (cm)	38.0
Packaging outer width (cm)	30.0
Packaging outer depth (cm)	26.0

SAFETY DATA

Glow Wire Test (°C)	650
Optimal operating condition (°C)	-20-40
Special purpose lamp	No
Dry applications use only	No
Suitable for household illumination	No