

NV dimmer for electronic transformers, R, C with ON/OFF pushbutton/selector switch FM, 230V 50-60Hz, 60-800 W/VA for claw and Screw mounting Screw terminals



Figure similar

Model	
product brand name	DELTA
product designation	LV dimmer
design of the product	Insert
type of load	other
type of composition	basic element
design of the operating mechanism	rotary knob/button
design of dimmer / series dimmer	No

General technical data	
operating apparent output / rated value	
• minimum	60 V·A
• maximum	800 V·A
dim power / minimum	0 V·A
mounting type	Claw and screw fixing
surface processing	other
material	other

Supply voltage

operating voltage / rated value	230 V
Protection class	
protection class IP	IP20
Current	
dim power / maximum	800 V·A
Main circuit	
operating frequency / rated value	
• minimum	50 Hz
• maximum	50 Hz
Suitability	
suitability for interaction	
• motion detector	No
• wireless pushbutton	No
• IR pushbutton	No
• presence detector	No
• pushbutton	No
• time switch	No
Appearance	
appearance	not applicable
color	miscellaneous
Product details	
product component	
• light value memory	No
• extension input	No
product feature	
• halogen-free	Yes
• transparent	No
Mechanical Design	
height	70 mm
width	70 mm
depth	35 mm
mounting type	flush mounting
material / of the enclosure	metal
Certificates	
reference code	
• acc. to DIN EN 61346-2	Q



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TC8258>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TC8258>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TC8258

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

