

GLE ELECTROVOLT

→ NATURAL RUBBER INSULATING GLOVES

► DESCRIPTION

Insulating rubber gloves available in all classes, many sizes, different lengths and colors. Leather protectors are recommended to be worn over Electrovolt gloves to ensure mechanical protection (local regulations, work practices and risk analysis apply).

► STANDARD

EN 60903:2003 - IEC 60903:2014
PPE Category III (Reg. EU 2016/425)



► TECHNICAL SPECIFICATIONS

Length : 41 cm

Available in 28 cm and 36 cm

Sizes : 6 to 12

Size 6 for class 00 and 0 only; class 3 and 4: 8 to 12

Color : Beige

Available in red and black

Refer to the table in the following page for more details

Class	Category	Thickness (mm)	Proof test voltage (V) / AC	Max operating voltage (V) / AC
00	AZC	< 1.1	2 500	500
0	AZC*	< 1,6	5 000	1 000
1	RC	< 2.1	10 000	7 500
2	RC	< 2,9	20 000	17 000
3	RC	< 3.5	30 000	26 500
4	RC	< 4.2	40 000	36 000

* RC version available on demand

► ADVANTAGES

The natural rubber provides high dielectric protection. The ergonomic shape and lightly powdered interior make the Electrovolt gloves easy for donning and doffing.

Document non contractuel pouvant être soumis à modification sans préavis

► **GLE: insulating rubber gloves beige color**

Class	Length (cm)	Sizes						
		6	7	8	9	10	11	12
00	28	GLE28-00/6	GLE28-00/7	GLE28-00/8	GLE28-00/9	GLE28-00/10	GLE28-00/11	GLE28-00/12
	36	GLE36-00/6	GLE36-00/7	GLE36-00/8	GLE36-00/9	GLE36-00/10	GLE36-00/11	GLE36-00/12
0	28	GLE28-0/6	GLE28-0/7	GLE28-0/8	GLE28-0/9	GLE28-0/10	GLE28-0/11	GLE28-0/12
	36	GLE36-0/6	GLE36-0/7	GLE36-0/8	GLE36-0/9	GLE36-0/10	GLE36-0/11	GLE36-0/12
	41	GLE41-0/6	GLE41-0/7	GLE41-0/8	GLE41-0/9	GLE41-0/10	GLE41-0/11	GLE41-0/12
1	36		GLE36-1/7	GLE36-1/8	GLE36-1/9	GLE36-1/10	GLE36-1/11	GLE36-1/12
	41		GLE41-1/7	GLE41-1/8	GLE41-1/9	GLE41-1/10	GLE41-1/11	GLE41-1/12
2	36		GLE36-2/7	GLE36-2/8	GLE36-2/9	GLE36-2/10	GLE36-2/11	GLE36-2/12
	41		GLE41-2/7	GLE41-2/8	GLE41-2/9	GLE41-2/10	GLE41-2/11	GLE41-2/12
3	36			GLE36-3/8	GLE36-3/9	GLE36-3/10	GLE36-3/11	GLE36-3/12
	41			GLE41-3/8	GLE41-3/9	GLE41-3/10	GLE41-3/11	GLE41-3/12
4	41			GLE41-4/8	GLE41-4/9	GLE41-4/10	GLE41-4/11	GLE41-4/12

► **SPECIAL GLOVES ON DEMAND**

Black color gloves : GLE B

Red color gloves : GLE R

Class 0 gloves RC : GLE 0 RC

► **ACCESSORIES**

Leather overgloves : RGX-SG

Talc bottle: RGX-FT

Transport bag : RGX-SAC

Pneumatic tester: RGX-VP

Cotton under gloves : RGX-GCT

Fingerless cotton under gloves : RGX-MC

Plastic transport and storage box : RGX-BG

Plastic transport and storage box with talcum bottle : RGX-BGT

Rubber cleaner bottle: RGX-1704 (1 bottle 750 ml)

Rubber cleaner carton : RGX-1704-PACK (16 bottles 750 ml each)