

Features

- Rotation Swivel
- Nylon
- Fixed Plate
- Brake
- Corrosion Resistant
- Impact Resistant

RS PRO Castor Wheels

RS Stock No.: 0631182



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description








Castors in zinc-chromium plated pressed steel, turning on double rim of balls. Nylon wheel. Recommended use for office furnitures, metal furnishing, electrical household, etc.

General Specifications

| | |
|---------------------------|---------------------------------------|
| Rotation | Swivel |
| Weight Class | |
| Load Capacity (Kg) | 40 |
| Load Capacity / 4pcs (Kg) | 120 |
| Tyre Material | Nylon |
| Hub Material | Nylon |
| Bracket Material | Pressed Steel |
| Includes Brake | Yes |
| Features | Corrosion Resistant, Impact Resistant |
| Applications | |

Operation Environment Specifications

| | |
|---------------------------------|--|
| Operating Temperature (Celsius) | |
|---------------------------------|--|

| | | | | | | |
|---|---|---|---|---|---|--|
|  |  |  |  |  |  |  |
| 50x23 | 29 | 40x40 | 42x42 | 6,5x10 | 75 | 40 |

Mechanical Specifications

| | |
|-----------------------------|-------------|
| Mounting Type | Single Bolt |
| Wheel Diameter (mm) | 50 |
| Wheel / Tread Width (mm) | 23 |
| Overall Height (mm) | 75 |
| Number of Fixing Holes | 4 |
| Fixing Hole Size (mm) | 6.5x10 |
| Hub Bearing Type | Plain Bore |
| Thread Size (M) | |
| Stem Height (mm) | |
| Stem Diameter (mm) | |
| Hardness of Wheel (Shore A) | |
| Levelling Extent (mm) | |
| Offset (mm) | |
| Castor Weight (Kg) | 0.270 |

Fixing Centres Specifications

| | |
|----------------------------|-------|
| Fixing Centres (mm) | 40x40 |
| Fixing Centres Length (mm) | 40 |
| Fixing Centres Width (mm) | 40 |

Fixing Plate Specifications

| | |
|------------------------------|-------|
| Fixing Plate Dimensions (mm) | 42x42 |
| Fixing Plate Length (mm) | 42 |
| Fixing Plate Width (mm) | 42 |