



2 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN Inspection Working Lamp WL280B

- Professional inspection lamp with the latest SMD LED technology
- Small spot light in the top of the lamp
- Robust and impact resistant plastic housing, particularly resistant to mechanical stresses – shockproof rating IK07
- Can be swivelled through 180°. Lamp grip can be locked in six positions for flexible lighting
- The robust belt clip has an integrated fold-out hook which can be swivelled through 360°
- Two strong mounting magnets on the underside of the lamp grip
- Battery operation with 3 x AA batteries
- Lighting power 280 lumens (main light) / 80 lumens (spot light)
- Battery life: ca. 8 hours / ca. 25 hours
- Incl. 3 x ANSMANN alkaline AA batteries
- 2 year ANSMANN guarantee

INFORMATION

Product name: WL280B
Article number: 1600-0179
EAN code: 4013674120529
Accessories incl.: 3 x AA alkaline batteries
Product: 190 x 60 x 40mm / 252g
Packaging + product: 272 x 125 x 50mm / 322g

Packaging unit: 6 (285x140x330mm)
Customs tariff number: 85131000

