

# 12V Max Portable Fan CXT

## CF101DZ

CF101D is a cordless fan powered by 12V max Li-Ion battery.



### TECHNICAL SPECIFICATIONS

Air Flow (H/M/L)	4.6 / 3.8 / 3.0 m <sup>3</sup> /min
Max Air Speed (Hi)	180 m/min
Max Air Speed (Lo)	120 m/min
Max Air Speed (Med)	150 m/min
Run Time (4.0ah) with Oscillation (H/M/L)	4.4 / 6.1 / 9.8 hrs
Battery Type	Lithium-ion
Body only machine	✓
Voltage	12 v
Diameter (D)	180 mm
Net weight	1.3 - 1.7 kg

### USER BENEFITS

- Compact size allows installation in confined spaces
- Automatic oscillation 45° Left / Right
- 3-Speed settings (Hi/Med/Low)
- Off-timer switch with 3 settings (1/2/4hrs) with LED display
- Adjustable fan head angle (up/down/left right)
- Adjustable hanging hook
- Screw hole for tripod mounting
- AC adaptor jack

[Link to product - www.makita.com](http://www.makita.com)



# RELATED PRODUCTS

(Recon

## ■ OTHER