

## Datasheet

### **RS Pro Anemometer, 30m/s Max Air Velocity**

RS Stock No: **724-4207**



## **Product Details**

RS Pro anemometer features LCD triple display. It has a maximum air velocity of 30 m/s. This anemometer includes data hold and maximum / minimum function. It comes with an auto power off and backlight function on/off time settings. This anemometer operates at a temperature rating of 0 to +50°C.

## **Features and Benefits**

- LCD triple display
- Auto power off function on/off time setting
- Backlight function on/off time setting
- Snake telescoping probe



ENGLISH

## Specifications:

Air Velocity Resolution	0.01 m/s
Battery Life	10 h
Battery Type	AAA
Best Air Velocity Accuracy	±3% +0.3 m/s
Dimensions	150 x 72 x 35 mm
Height	35 mm
Length	150 mm
Maximum Air Velocity	30 m/s
Maximum Operating Temperature	+50°C
Measurement Parameters	Volume Air Flow
Minimum Operating Temperature	0°C
Power Source	Battery
Probe Type	Hotwire
Weight	400 g
Width	72 mm
Display Type	LCD