

Features

- High conductivity
- Corrosion resistant
- Vinyl insulated
- Vibration resistant

RS PRO Yellow Double Crimp Ring M8

RS Stock No.: 0677147



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Ensure reliable and safe electrical connections with our high-quality insulated double copper sleeve terminals. These terminals provide superior conductivity feature a protective tin plating to resist corrosion. The durable insulation adds an extra layer of safety, preventing short circuits and ensuring long-lasting performance. Their dual-grip design provides a secure hold, even under high vibration, making them ideal for demanding applications.

General Specifications

Type	Double Copper Sleeved
Connector Type	Ring
Contact Plating	Tin
Contact Material	Copper

Electrical Specifications

Insulation Material	PVC
Stud Size	M8
Wire Entry	5mm 12-10AWG


Operation Environment Specifications

Temperature Rating	75°C max
--------------------	----------

Approvals

Compliance/Certifications	REACH, RoHS, UL
---------------------------	-----------------

Declarations



Drawing Specifications

Od2	8.4mm
W	15.0mm
F	13.5mm
L	35.0mm
B	14.0mm
OD	6.8mm
Od1	3.4mm
T	1.0mm
Size	5-8
AWG	12-10
Colour	Yellow