

Product datasheet

Specifications



switch disconnector iSW - 4P - 100 A - 415 V

Local distributor code:
399368424

A9S66491

EAN Code: 3606480531453

Main

Range	Acti9
Product name	Acti9 iSW
Product or component type	Switch disconnector
Device short name	iSW
Device application	Control Isolation
Poles description	4P
Utilisation category	AC-22A
Suitability for isolation	Yes

Complementary

[Ie] rated operational current	100 A at 415 V AC 50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
[Icm] rated short-circuit making capacity	5 kA switch-disconnector alone
[Icw] rated short-time withstand current	1500 A
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	73 mm
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - terminals	Tunnel type terminals (top or bottom) - <= 1 x 50 mm² - rigid Tunnel type terminals (top or bottom) - <= 1 x 35 mm² - flexible Tunnel type terminals (top or bottom) - <= 1 x 35 mm² - flexible with ferrule
Wire stripping length	14 mm
tightening torque	3.5 N.m

Environment

Standards	BS EN 60947-3 AS 60947-3 NZS 60947-3 IEC 60947-3 EN 60947-3
IP degree of protection	IP20
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	6 cm
Package 1 Weight	335 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	8 cm
Package 2 Width	22 cm
Package 2 Length	9.5 cm
Package 2 Weight	1.05 kg
Unit Type of Package 3	S03
Number of Units in Package 3	33
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	12.521 kg

Logistical informations

Country of origin	HU
-------------------	----

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	201
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	E5f22bd9-8e0c-4771-b932-618a392a4c8b
REACH Regulation	REACH Declaration
Halogen-free status	Halogen free plastic parts product

Use Again

 Repack and remanufacture	
End of life manual availability	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins