



## GBC Inspire+ A3 Laminator

Lightweight and compact, the Inspire+ A3 Laminator is perfect for the occasional home or office user who needs the flexibility to produce items from ID up to A3 size. It is really simple to operate via a single switch and takes standard 2x75 micron pouches, while the exit tray ensures a perfectly flat finish. Get creative with the Inspire+ - imagination is all you need!



A3  
4 Min  
72 Sec A4

≤ 125 Mic

180 mm  
445 mm  
80 mm

signs.gbceurope.com

## Attributes

- A3 laminator
- Warms up in 5 minutes
- Uses 2x75 micron pouches
- Laminates from ID to A3 size
- Cold setting for use with self-adhesive cold seal pouches
- For best results use with GBC document pouches

## Specifications

Number	4402076
Colour	black
Dimensions (W x H x D)	140 x 60 x 445 mm
Laminating Speed (mm/min)	250
Power Supply	220/240 V AC
Warm up Time (min)	4
Heating System	2 heated rollers
Operation Mode	2 roller, no carrier, temperature controlled
Max. Laminating Width (mm)	303
Max. Laminating Thickness (mm)	0.5
Max. Pouch Thickness (microns)	75
Power Consumption (W)	550
Dimensions (with Tray) mm	440(W) x 60(H) x 125(D)
Anti-Jam Technology	Manual Release
Approx. lamination time (A4)	72 secs (A4 75 microns)
Photo friendly	Yes
Type	Pouch
Weight	1680 g
Pallet quantity	140
EAN code	5028252502726