



fitted with

- work equipment**
- connected load**
- power consumption**
- light distribution**
- glare-free**
- system of protection**
- class of protection**
- usage**
- luminaire body**
- weight (net)**
- mains supply**

- fastening**
- dimension**
- light output**
- outside diameter**
- side part**

- 1 x compact fluorescent lamp TC-LEL 24W/840 2G11
- light colour neutral white, 4000 K, Color Rendering Index (CRI)=80
- Energy efficiency category B
- electronic ballast
- 100-250 V; 50/60 Hz
- approx. 25 W
- direct
- aluminiumised parabolic louvre
- IP 67
- I
- without switch
- acrylic (PMMA), clear,
- approx. 1.5 kg
- connection box
- 160 BU/3
- lamp bracket (accessory)
- A=495 mm
- D=331 mm
- 70 mm
- C with screwed cable gland



160 BU/3

illuminance

measuring conditions: d=100cm

Em: 196 lx
Emax: 257 lx
Emin: 124 lx

