
SPOT LED 8 W 3000 K IP65 FP DIM SL

LEDVANCE SPOT LED FIREPROOF | LED spotlight luminaires



Areas of application

- Replacement of conventional 50 W halogen spotlights
- Hotel rooms
- Bars, restaurants
- Bathrooms
- Accent lighting
- Galleries, museums
- General illumination
- Outdoor

Product benefits

- Design matches the LEDVANCE DOWNLIGHT luminaire family
- Energy savings of up to 90 % compared to halogen lamp spotlights
- Functional and minimalistic design
- Easy installation with fast connection
- External driver for extended flexibility (compatible with selected dim. drivers)
- Designed for extra IP protection
- 3 years guarantee

Product features

- Luminous efficacy: 75 lm/W
- Luminous flux: 530 lm
- Compatible with standard ceiling cutouts of 68 mm
- Color temperature: 3,000 K
- Initial color consistency: ≤ 4 SDCM
- Beam angle: 38°
- Type of protection, front side: IP65



Product datasheet

- Lifetime: up to 30,000 h
- Certificates: CE, CB, TUEV SUED

Technical data

Electrical data

Operating mode	Electronic control gear (EVG)
Nominal wattage	8.00 W
Nominal voltage	220...240 V
Mains frequency	50/60 Hz

Photometrical data

Color temperature	3000 K
Luminous flux	620 lm
Light color (designation)	Warm White
Color rendering index Ra	>80

Light technical data

Beam angle	36 °
------------	------

Dimensions & weight

Diameter	81.0 mm
Height	51.0 mm
Mounting diameter	68 mm

Colors & materials

Body material	Aluminum
Product color	Silver

Temperatures & operating conditions

Ambient temperature range	-20...45 °C
---------------------------	-------------

Lifespan

Lifespan	30000 h
----------	---------

Capabilities

Dimmable	Yes
----------	-----

Certificates & standards

Protection class	II
Type of protection	IP65

Product datasheet

Safety advice

Fire-resistant (up to 90 minutes fire rating, BS476-20:1976 and BS476-21:1976)

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075811218	SPOT LED 8 W 3000 K IP65 FP DIM SL	Shipping carton box 27	440 mm x 320 mm x 360 mm	50.69 dm ³	10.11 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
