

NEOPRENE SPONGE

STOCK NO. SIZE

303-2218 1m x 2m x 1.5mm
303-2252 1m x 2m x 3mm
303-2246 1m x 2m x 6mm
303-2230 1m x 2m x 10mm
303-2224 1m x 2m x 16mm
303-2268 1m x 2m x 20mm

Closed Cell sponge.

Cell/Cell finish


Colour - Black

Density - 120 Kg/m³

Spec - ASTM D1056-85 2C2

Temperature : -30°C to +100°C

Good Recovery, Oil, Weather and
Ozone resistance.



POLYETHYLENE FOAM

STOCK NO. SIZE

303-2274 1m x 2m x 3mm
303-2280 1m x 2m x 6mm
303-2296 1m x 2m x 10mm

Closed Cell Foam.

Cell/Cell Finish


Colour - Black

Density - 45 Kg/m³

Temperature : -70°C to +110°C

Good Oil and Weather resistance.

Food Quality.



SILICONE SPONGE

STOCK NO. SIZE

303-2303 1m x 0.6m x 1.5mm
303-2319 1m x 0.6m x 3mm
303-2325 1m x 0.6m x 6mm

Closed Cell Sponge.

Skin/Skin finish

Colour - White

Density - 250 Kg/m³

Temperature : -60°C to +200°C

Good Weather , UV, and Ozone
resistance.

