

**ZMA90/155** **Precision locknut**

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information**Main Dimensions & Performance Data**

d	M90X2	Thread
D	155 mm	Outside diameter
h	38 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	1,080,000 N	Breaking load, axial
M _L	360 Nm	Breakawag
M _{AL}	200 Nm	Mounting torque reference
M _M	150 kg*cm ²	Mass moment of inertia
≈m	3.36 kg	Weight

Dimensions

d ₁	146 mm	Plant diameter outside
t	4 mm	Hight retaining slot
b	10 mm	Width retaining slot
c	19 mm	Distance bore
m	M8	Threaded - threaded pin