



Main

Range	Exiway
Product name	Exiway Easysign
Product or component type	Emergency exit sign
Device application	Lighting
Function	Standard
Supply	Maintained Non-maintained
Number of batteries	1 LiFePO4
Colour	White (RAL 9010)
Light source	1 x LED
Visibility distance	24 m

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Electrical insulation class	Class II
LED lifespan	100000 h
Autonomy	1.5 h
Local signalling	Indicator light
Material	Plastic self-extinguishing
Device mounting	Recessed ceiling
Height	170 mm
Width	260 mm
Depth	31 mm

Environment

IP degree of protection	IP40
IK degree of protection	IK04
Ambient air temperature for operation	0...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	550 g
Package 1 Height	3.1 cm
Package 1 width	17 cm
Package 1 Length	26 cm

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins