

RT4FC-B

4 pole female TINY xIr cable connector





Article Variations

Article Name	Details	Packaging
RT4FC-B	Black plated housing, gold plated contacts	Plastic Bag
RT4FC-B-D	Black plated housing, gold plated contacts	BULK
RT4FC-B-W	Black plated housing, gold plated contacts, water resistant boot	Plastic Bag
RT4FC-B-W-D	Black plated housing, gold plated contacts, water resistant boot	BULK



Product Title Connection Type

Electrical			
Contact Resistance	≤10 mΩ		
Insulation Resistance	>1 GΩ		
Dielectric Strength	>500 V rms		
Rated current per contact	5 A		

Mechanical		
Cable O.D. Range	2.0-4.5mm	
Lifetime	>1000 Mating Cycles	
Wiresize	0.22 mm ²	
Wiresize	24 AWG	



Material		
Ground Contact	Steel	
Rubber Spring	Rubber	
Latch	Zinc	
Chuck	POM	
Boot	PC/ABS+TPU	
Housing	Zinc	
Plastic housing	PA6+30%GF	
Jack	Bronze	
Ground Contact	Bronze	
Tube	Aluminum	
Latch	Nickel Plating	
Housing	Nickel Plating	
Jack	Gold Plating	
Ground Contact	Tin and Cer	
Tube	Black Plating	