

Datasheet

RS Pro Square Fixed Height Feet, PD.2126BL PUR, +65°C - 34°C

RS Stock No: **223-657**



Product Details

RS Pro square anti-vibration feet in black colour, is made with PUR for long life durability. It has a overall height of 5.8 mm. It features excellent skid resistance with a high coefficient of friction and excellent resistance to moving and staining. It has a temperature rating of -34 to +65°C. Self adhesive polyurethane bumper/feet helps to sound-dampen, absorb shock, prevent items from moving/slipping and act as general buffers. It may be easily applied to clean, dry, free from-dirt/grit surfaces on furniture, electrical and electronic equipment and accessories and point-of-sale equipment.

Features and Benefits

- Long ageing resiliency and will not crack or harden
- Ideal for use on glass, aluminium, stainless steel, acrylic plastic, polyethylene, polystyrene, ABS, polypropylene and polycarbonate
- To ensure maximum adhesion, surfaces must be clean, dry and well unified
- Flexible polyurethane feet suitable for indoor and limited outdoor applications

Specifications:

Foot Colour	Black
Foot Shape	Square
Material	PUR
Mounting Type	Adhesive
Type	Feet
Maximum Operating Temperature	+65°C
Minimum Operating Temperature	-34°C
Overall Height	5.8 mm
Finish	Gloss
Hardness	65 to 70 Shore A
Width	12.7 mm