



182.72.104.66NX..-ZNadel-Axialkugellager

Needle roller/axial ball bearings

NX17-Z-XL (Series NX..-Z)

single direction axial component, for grease lubrication

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	17 mm
D	26 mm
C	28 mm Tolerance: 0/-0,25
2)	Mounting dimensions Snap ring in outer ring
C1	8 mm
C2	12,2 mm
D1	28,5 mm
da	21 mm
dw	17 mm Tolerance: E8
ra max	0,3 mm
rmin	0,3 mm
m	53 g Mass
Cr	13500 N Basic dynamic load rating, radial
Cor	15000 N Basic static load rating, radial
Ca	5800 N Basic dynamic load rating, axial
Coa	11500 N Basic static load rating, axial
Cur	2750 N Fatigue limit load, radial
Cua	510 N Fatigue limit load, axial
ng	7500 1/min Limiting speed
	IR14X17X17-XL Suitable inner ring
	WR26, Suitable snap rings WR and SW SW26

