


# Manifold block-SET VABS-C12-6-S-B3

Part number: 8122792

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Construction width	6 mm
Mounting position	optional
Design	Connection direction at side
Max. number of valve positions	1
Operating pressure	-0.1 MPa ... 0.7 MPa
Operating pressure	-1 bar ... 7 bar
Operating medium	Compressed air to ISO 8573-1:2010 [6:4:1]
Note on operating and pilot medium	Maximum particle size 5 µm
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	5 °C ... 50 °C
Product weight	1.1 g
Type of mounting	With through-hole
Pneumatic connection, port 2	For tubing I.D. 2 mm
Note on materials	RoHS-compliant
Material manifold rail	PBT