



MIDI 40-PP10

Blade Fuse, Midi (ATO, Norm), 40A, Orange

Product Properties:

Release characteristic	Fast (F)
Rated voltage	32 V
Type of current	DC
Colour code	Other
Nominal voltage DC	32 V
Number of fuses	10 .
Model	Blade fuse
Max. current (I _{max})	40 A
Nominal current	40 A
Fuse type	Midi

Dimensions:

Width	18.8 mm
MOQ	10 .
Unit	pck
Rated voltage	32 V
Length	18.7 mm

Approvals:

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)

SCIP

Not Applicable

Other information:

ETIM-Class	EC002298 - Blade fuse
ETIM-Release	9.0
Trademark	NECORE
Product Group	Blade fuses - Pin-pac
Search Description	FLATSÅKRING, MIDI (ATO, NORM), 40A
Alternative SKU	MIDI40-PP10

Logistic information:

Barcode	733117618641
Country of origin	TW
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	MIDI 40-PP10
Taric code	85361050
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.