



36W A FRAME PLASTERERS LIGHT

Installer Guide

SECTION ONE GENERAL INFORMATION

Do not use this unit in situations where flammable liquids, vapours or gases are present.
Do not allow this unit to get wet in storage or in use.
Do not use if the cable is damaged in any way.
The cable is not replaceable and if damaged this product must be discarded.

PARTS INCLUDED

- A Frame and Light enclosure, 5m cable with 110V UK plug
- Instruction manual. Please keep safe for future reference.
- 2 x 18W 110V fluorescent bulbs

SECTION TWO BULB FITTING AND REPLACEMENT

The A Frame is fully assembled on purchase. When in use ensure that the unit is on a flat, stable platform and ensure that the legs are extended outwards to the maximum position.

Unclip the plastic clips that run down each side of the light enclosure.
This will release the cover.

A spare clip is provided in case of any breakages.

Fit the fluorescent tubes ensuring that the bulb is sat correctly at each end.

Replace the front cover then re insert and close the clips. When closed correctly the clips will fit flush to the casing.

Turn on the power supply.

IMPORTANT

This unit must only be connected to an appropriate 110V power supply/transformer
The unit has the additional feature of 2 x 16 amp 110V power sockets.

TECHNICAL SPECIFICATIONS

Power Supply	110V ~ 50Hz
Lamp Type	2 x 18W 110V T8 Fluorescent tube MAX
Environmental Protection	IP44 (suitable for outdoor use)

