

Previously known as: Powerflex® 80-658



Cut



Heat



Heavy Duty

High-performance protective gloves, combining cut and heat resistance with excellent grip

- **Advanced defenses:** ActivArm® 80-658 safety gloves' steel, fiberglass and aramid liner affords EN ISO E cut resistance, as well as EN 407 level 2 heat contact resistance, for superior hand protection when handling sharp and warm components
- **Specialized protection:** With their latex coating and raised crinkled finish, these sturdy heavy-duty gloves reduce slippage and muscle tension, protecting hands while ensuring strong grip performance
- **Enhanced features:** For added forearm and wrist protection, ActivArm® 80-658 industrial gloves feature an extra-long, three quarter-dipped, liquid-repellent cuff, shielding the skin from potentially hazardous liquid solutions
- **Added convenience:** These heather green-colored gloves mask dirt, while remaining washable and available in varying sizes



Industries

- Construction
- Glass manufacturing
- Metal fabrication
- Recycling and Waste Disposal

Applications

- Heavy duty handling: where sensitivity is also required
- Handling jagged metal
- Handling of glass sheets, sharp edged objects
- Handling of metal sheets, cutting of dry, painted or galvanised pieces

Previously known as: Powerflex®80-658

Key Features

- **Three-layer construction:** Added cut, splinter and burn resistance
- **Latex coating with crinkled finish:** Firm dry and wet grip
- **Extra-long cuff:** For work gloves offering forearm and wrist protection

Vulcanization Chemical Accelerators

- Natural rubber proteins (in the coating and in the elastic cuff)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 80-658	Finishing: Dipped Coating Material: Natural Rubber Latex Liner Material: Stainless steel, Nylon, Fiber glass, Cotton, Aramid Cuff Style: Extra Long	7	6, 7, 8, 9, 10	250-300 mm; 9.84-11.81 inches	Blue	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699