

## Features

- Ideal to work in Hard-to-Reach Areas
- Used for finishing, removing weld seams, burrs, and defects on surfaces like metal and wood.
- Slotted rubber construction improves airflow and temperature resistance while securely fixing the abrasive.
- Suitable for both pneumatic and portable power tools.

## RS PRO Backing Pads & Mandrels

RS Stock No.: 0768413, 0768415, 0768417, 0768231, 0768233, 0768235, 0768237, 0768241, 0768242, 0768244, 0768248, 0768249, 0768252



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*Expanding rubber holders are the ideal solution for working in hard-to-reach areas. They are primarily used for finishing, removing weld seams, burrs, and other defects from various surfaces such as metal and wood.*

*Their special slotted rubber design ensures better airflow and increased temperature resistance, while simultaneously securely fixing the abrasive material in place (which must be purchased separately).*

*Featuring durable 6 mm metal shafts, these drum holders are compatible with both pneumatic tools and portable power tools.*

## General Specifications

<b>Holder Types</b>	Cylindrical (D x H x S) and Conical (D1 x D2 x H x S)
<b>Shaft Diameter (S)</b>	6 mm

## Mechanical Specifications

### A. Cylindrical Rubber Mandrels (Compatible with cylindrical sanding drums)

Article Code	Dimensions (D x H x S) [mm]	Maximum Speed [min <sup>-1</sup> ]	Compatible Cylindrical Sanding Drum Size
0768413	15 x 30 x 6	26000	15 x 30
0768415	19 x 25 x 6	20000	19 x 25
0768417	22 x 20 x 6	17000	22 x 20
0768231	25 x 25 x 6	15000	25 x 25
0768233	30 x 20 x 6	13300	30 x 20
0768235	30 x 30 x 6	13300	30 x 30
0768237	38 x 25 x 6	11000	38 x 25
0768241	45 x 30 x 6	8500	45 x 30
0768242	51 x 25 x 6	7000	51 x 25
0768244	60 x 30 x 6	6500	60 x 30

## B. Conical Rubber Mandrels (Compatible with conical sanding drums)

Article Code	Dimensions (D1 x D2 x H x S) [mm]	Maximum Speed [min <sup>-1</sup> ]	Compatible Conical Sanding Drum Size
0768248	20 x 14 x 63 x 6	13000	20 x 14 x 63
0768249	29 x 22 x 30 x 6	13000	29 x 22 x 30
0768252	36 x 22 x 60 x 6	5000	36 x 22 x 60