


Technical data sheet

Article number:
111-00969

T50R



Product Group	Cable Ties for temperatures up to + 195 °C (500 h) in Polyamide 4.6
Product Family	T-Series in PA46
Material	Polyamide 4.6 (PA46)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Length (L)	202 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +130 °C, (+150 °C, 5000 h; +195 °C, 500 h)
Pack Cont.	100 pcs.
Releasable Closure (Yes/No)	No
Specifications	ANSI/UL 62275, csa-C22.2 no. 62275
Thickness (T)	1.2 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E85319
UV-resistant acc. to ASTM D6779 (Yes/No)	No
Variant	Inside Serrated
Weight/Unit	0.0013 kg
Width (W)	4.6 mm

