



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 2-2083073-5

Cable Assy Nector S Plug to Outlet UL

TE Part # 1-2368264-1

C/A Nector S Distr to Powerplug HV-4 Whi

Customers Also Bought



TE Part #1-2176403-9

3550 5R6 1%



TE Part #2-2176403-2

3550 7R5 1%




TE Part #3-2176430-5

MPT35 1R8 1%



TE Part #2-1423675-0

W57-XB2A99C10-5=CKTBKR,THERM,P



TE Part #1-1879628-9

H4P 750K 1% 100PPM



TE Part #2-2083075-1

C/A Nector S Plug to Pigtail LV-2 SVT Wh



TE Part #2-2083077-1

C/A Nector S Outlet to Pigtail LV-2 SVT




TE Part #85875-7

02 MODI HDR SRST .156CL



TE Part #293649-2

NECTOR S T-SPLITTER SWITCH VERSION LV2



TE Part #8-2176379-8

RQ 0805 866R 0.1% 10PPM 5K RL

Documents

Product Drawings

Cable Assy Nector S Plug to Ou

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2083073-1_E.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-2083073-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2083073-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English