


## WSL-M6

### Tool trolley workster smartline

with 6 drawers

Code 3100707	ETIM EC011808
EAN 4010886952511	UNSPSC 56-12-18-02
Country of origin Germany	eCI@ss 21-07-11-00
Customs tariff number 94032080	



### Article description

- Body:
  - Dimensions: H 903x B 629x D 510 mm
  - Work platform with ABS plastic cover with frontal flattening and roll protection edge
  - Manoeuvrable and easy to steer with drive/steer handle
  - Side walls with Euro perforation 10 x 38 mm for attaching hooks and tools
  - Sides rounded off – a minimum of abutting edges
  - Body welded, self-supporting and torsionally rigid
  - Sheet steel, corrosion resistant and scratch-proof powder-coated
- Drawers:
  - Single pull-out stop prevents more than one drawer from being opened, one-hand operation
  - Central locking with cylinder lock
  - 6 wide drawers (W 480 x D 400 mm) fully extending
  - Guide rails with ball bearings
  - Load capacity per drawer 20 kg
  - Sheet steel, corrosion and scratch-resistant, powder-coated
  - GEDORE chassis: • Total load capacity 300 kg
  - 4 smooth running wheels on ball bearings (swivel castors Ø 125 mm) with thread guard, one with total brake
  - Also in case of maximum loads: smooth running, manoeuvrability and track-keeping
  - Options:
    - Can be equipped with GEDORE tool modules (1500 ES/1500 CT)
    - Can be individually subdivided with lengthwise and crosswise dividers
    - Delivery without tools and accessories

### Article information

Contents (Qty of pieces)	1	Load capacity per drawer [kg]	20 kg
Net weight [kg]	48 kg	Drawer type	5x Type 1, H = 80 mm 1x Type 2, H = 160 mm
Total length [mm]	625 mm	Fixed roller diameter (2x)	125
Total width [mm]	510 mm	Swivel castor diameter with brakes (2x)	125
Total height [mm]	900 mm	Single pull-out stop	yes
Material	sheet steel	Number of wheels	4
Colour	GEDORE blue, RAL 5017	Working height	900
Number of drawers	6	Static load carrying capacity [kg]	300 kg