

1 B 38

Combination spanner with same size each end

metric

Code **6003500** ETIM **EC002176**

EAN **4010886600351** UNSPSC **27-11-17-13**

Country of origin **Germany** eCl@ss **21-04-01-05**

Customs tariff number
82041100



Article description

- Acc. to DIN 3113, Form A, ISO 3318, ISO 7738
- Sizes 5 and 5.5 mm with hexagon ring, up from size 6 mm with UD profile
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Ring: 10° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- The offset ring ensures a better grip on deep-seated or inset nuts or bolts
- Top-grade industrial quality for the hardest of continuous use
- * not standardised

Article information

Contents [Qty of pieces]	1	Width of head 2 [mm]	79,2 mm
Net weight [kg]	1,081 kg	Head height 2 [mm]	13,2 mm
Total length [mm]	460 mm	Head height 1 [mm]	24,2 mm
Total width [mm]	75 mm	Width of head 1 [mm]	56,0 mm
Total height [mm]	44 mm	Mouth position 1	15°
Surface	chrome-plated	Height of offset 1	43 mm
Material	Vanadium steel 31CrV3	Ring profile	UNIT-DRIVE
Standard	not standardised	Ring offset	10°
Width across flats 1 [mm]	38	Weight	2,380 lbs