

**Schneider Electric USA**

1415 South Roselle Road

Palatine, IL 60067

Customer Care Center: 1-888-778-2733

Web: www.schneider-electric.us

**Item # ABL1RPM12083, Dedicated Power Supplies****Dedicated Power Supplies**

Power Supply 12Vdc 8.3 Amp

**SPECIFICATIONS**

Input Voltage	100-240 Vac 50/60Hz, single phase
Output Voltage	12Vdc
Nominal Power	100 Watts
Nominal Current	8.3 Amp
Reset	Automatic
Mounting	DIN Rail (with mounting kit) / Panel / Mounting bracket
Screw Size for Panel Mounting	# 8-32
Wire Range (AWG)	#14 - #18
Tightening Torque	7 lb-in (0.8 Nm)
Conform to EN61000-3-2	Yes
UL File	E164867 NMTR, E164867 NMTR7
CSA File	204701 5311-07, 204701 5311-87
CE	Yes
RoHS	Yes
Weight	1.41 lb (0.64 kg)