

## RAFIX insulated housing 16 mm, 4 mounting positions, light gray

### REPLACEMENT



### fields of application

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Industrial robots

## description

### technical data

#### ➤ general

Installation points	4 pcs.
Color	light gray
Packaging unit	1 pcs.
net weight	298 g
Degree of protection, front side, according to DIN EN 60529	IP65
Degree of protection, rear side, according to DIN EN 60529	IP65
MOQ order	5 pcs.
RoHS compliant	Yes
REACH compliant	Yes

#### direct links

- [RAFI eCatalog](#)

#### ➤ mounting diameters

Outside dimension, length	100 mm
Outside dimension, width	145 mm
Outside dimension, height	74 mm
Mounting hole	16.2 mm

**drawings****Dimensioned drawing**