



PRODUCT NUMBER: 4580130

DexPure 801-30

Preparation of slightly greasy or non greasy products (fruits and vegetables, white meat).

Cleaning and maintenance.

Honeywell

Overview

Reference Number

4580130

Product Type

Gloves

Range

Chemical Protection

Line

Disposable

Brand

Honeywell

Brand formerly known as

SPERIAN

Industry

- Automotive and Part Manufacturer
- Aviation
- Catering
- Chemical Industries
- Food Industries
- Industrial Cleaning
- Laboratory
- Maintenance
- Petro-chemical
- Printing Industries
- Water treatment
- Medical & Pharmaceutical

Product Use

Preparation of slightly greasy or non greasy products (fruits and vegetables, white meat).

Cleaning and maintenance.

Features & Benefits

Feature

100% heavy disposable latex glove

Powder-free

Raised pattern

Rolled cuff

Benefit

COMFORT

Disposable glove for an excellent touch.

Its patterned finish provides a better grip.

RESISTANCE

The glove is made from pure natural latex.

Regular controls ensure a very low residual protein rate.

The glove's mechanical resistance and thickness make it an economical alternative to the traditional reusable model.

HYGIENE

The glove is treated to prevent the development of bacteria.

Certified for contact with food.

Its non-powdered interior ensures the absence of a transfer of corn starch to foodstuffs and a low risk of allergy.

Its blue colour, easy to detect, makes it suitable for the agrifood industry.

Technical Description

Description

CE CATEGORY : III Irreversible or lethal risks

In accordance with standards :

EN 420:2003+A1:2019 – Basic requirements

EN 388:2016+A1:2018 (0110X) – mechanical hazards

EN ISO 374-1:2016 / A1:2018 – Type C – Chemical hazards

EN ISO 374-5:2016 – Microorganisms

EN 455 - Medical gloves for single use

Regulation (EC) 1935/2004 – Food contact

Characteristics

Heavy unlined disposable glove, 100% latex powder- free, raised pattern, rolled cuff , AQL 1,5

Product Technology

Dipped Gloves

Glove/liner color

Blue

Coating Type

Latex

Length

30 cm

Thickness

0,3 mm

Harmlessness

In conformity with the European standards

Dexterity

Class 5

Sizes

7 to 10

EN 388 - Mechanical resistance

Abrasion resistance	0
Cutting resistance (Coupe test)	1
Tear resistance	1
Puncture resistance	0
Cutting resistance (TDM test)	X

EN ISO 374-1 Resistance to permeation by chemicals

Type C

Tested chemicals :

- Sodium hydroxide 40% (K)
- Sulfuric acid 96 % (L)

Certifications

EU Category PPE

3

EU Certification

0075/797/162/04/19/1314

Additional Information

User Manual

UI 244

Maintenance

Storage Information

Minimum packaging 1 box of 50 gloves.

Cartons of 10 boxes.

Instructions for use printed on the box.

Care Instructions

In order to keep its properties, this article should not be cleaned.