

















 Series 4		 Series 5		 Series 22		 Series 13						
													
	 K 35/4	 EK 35/4-L	 EK 50/5-L			 K22	 HK 60/22	 EK 60/22-L	 EK 60 UNV-L	 HK 120/42	 HK 120 U	 EK 120/42-L	 EK 120 U-L
Copper tubular cable lugs and connectors Series L	HL46	6 mm ²	HL5635	6 + 35 mm ²	L226	6 mm ²	HL136	6 mm ²					
	HL410	10 mm ²	HL51050	10 + 50 mm ²	L2210	10 mm ²	HL1310	10 mm ²					
	HL416	16 mm ²	HL51670	16 + 70 mm ²	L2216	16 mm ²	HL1316	16 mm ²					
	HL425	25 mm ²	HL52595	25 + 95 mm ²	L2225	25 mm ²	HL1325	25 mm ²					
	HL435	35 mm ²	HL5120	120 mm ²	L2235	35 mm ²	HL1335	35 mm ²					
	HL450	50 mm ²	HL5150	150 mm ²	L2250	50 mm ²	HL1350	50 mm ²					
	HL470	70 mm ²	HL5185	185 mm ²	L2270	70 mm ²	HL1370	70 mm ²					
	HL495	95 mm ²	HL5240	240 mm ²	L2295	95 mm ²	HL1395	95 mm ²					
	HL4120	120 mm ²			L22120	120 mm ²	HL13120	120 mm ²					
	HL4150	150 mm ²			L22150	150 mm ²	HL13150	150 mm ²					
Stainless steel and nickel tubular cable lugs and connectors	HN4051	0.5-1.0 mm ²			N2210	10 mm ²							
	HN41525	1.5-2.5 mm ²			N2216	16 mm ²							
	HN446	4-6 mm ²			N2225	25 mm ²							
	HN410	10 mm ²			N2235	35 mm ²							
	HN416	16 mm ²			N2250	50 mm ²							
Copper compression cable lugs (DIN 46235) and connectors (DIN 46267, part 1) acc. to DIN	HD46	6 mm ²	HD5635	6 + 35 mm ²	D226	6 mm ²							
	HD410	10 mm ²	HD51050	10 + 50 mm ²	D2210	10 mm ²							
	HD416	16 mm ²	HD51670	16 + 70 mm ²	D2216	16 mm ²	HD1316	16 mm ²					
	HD425	25 mm ²	HD52595	25 + 95 mm ²	D2225	25 mm ²	HD1325	25 mm ²					
	HD435	35 mm ²	HD5120	120 mm ²	D2235	35 mm ²	HD1335	35 mm ²					
	HD450	50 mm ²	HD5150	150 mm ²	D2250	50 mm ²	HD1350	50 mm ²					
	HD470	70 mm ²	HD5185	185 mm ²	D2270	70 mm ²	HD1370	70 mm ²					
	HD495	95 mm ²			D2295	95 mm ²	HD1395	95 mm ²					
	HD4120	120 mm ²			D22120	120 mm ²	HD13120	120 mm ²					
					D22150	150 mm ²	HD13150	150 mm ²					
Copper solderless terminals (DIN 46234), pin terminals (DIN 46230) acc. to DIN -Cu and connectors (DIN 46341) acc. to DIN	HQ410	10 mm ²	HQ510	10 mm ²	Q2210	10 mm ²							
	HQ416	16 mm ²	HQ516	16 mm ²	Q2216	16 mm ²	HQ1316	16 mm ²					
	HQ425	25 mm ²	HQ525	25 mm ²	Q2225	25 mm ²	HQ1325	25 mm ²					
	HQ435	35 mm ²	HQ535	35 mm ²	Q2235	35 mm ²	HQ1335	35 mm ²					
			HQ550	50 mm ²	Q2250	50 mm ²	HQ1350	50 mm ²					
					Q2270	70 mm ²	HQ1370	70 mm ²					
							HQ1395	95 mm ²					
							HQ13120	120 mm ²					
						HQ13150	150 mm ²						

>>>