



**Part Number :** [732520092](#)

**Product Description :** Precision Test Connector, 2.92mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, without Screws, 50 Ohms

**Series Number :** 73252

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents & Resources


### Drawings

[732520092\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant   |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21   |
| REACH SVHC         | Contains Lead per D(2023)8585-DC<br>(23 Jan 2024)  |
| EU RoHS            | Compliant with Exemption 6(c) per<br>EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|              |  |
|--------------|--|
| Status       | Active   |
| Category     | RF / Coaxial Connectors  |
| Series       | 73252  |
| Description  | Precision Test Connector, 2.92mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, without Screws, 50 Ohms |
| Application  | RF   |
| Comments     | Solderless Compression   |
| Product Name | Precision Test - 2.92mm  |
| Style        | PCB  |
| Type         | Subminiature   |
| UPC          | 884982956001   |

#### Electrical

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 40 GHz                      |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 500 Vrms@Sea Level |

#### Physical

|                       |                             |
|-----------------------|-----------------------------|
| Cable Attachment      | N/A                         |
| Gender                | Jack                        |
| Keying to Mating Part | N/A                         |
| Net Weight            | 1.848/g                     |
| Orientation           | Straight                    |
| Packaging Type        | Tray                        |
| Panel Mount           | No                          |
| Panel Mount Method    | N/A                         |
| PCB Mounting          | Surface Mount - Compression |

|                             |         |
|-----------------------------|---------|
| PCB Thickness - Recommended | Various |
| Reverse Polar               | No      |
| Wire/Cable Type             | N/A     |

**Solder Process Data**

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|