



Operational characteristics

Rated supply voltage AC	VAC	380...440
Rated frequency	Hz	45...65
Holding consumption	VA	1.67
Release voltage	Us	35...70
Operating voltage	US	85...110
Average opening time	ms	50

Mechanical features

Tightening torque for terminals	min	Nm	0.8
	max	Nm	1
	min	lbin	7
	max	lbin	9
	<hr/>		
Conductor section	AWG/Kcmil		
	min		20
	max		16
	Flexible w/o lug conductor section		
	min	mm ²	0.5
	max	mm ²	1.5
<hr/>			
Flexible c/w lug conductor section			
min	mm ²	0.5	
max	mm ²	1.5	
<hr/>			
Terminals	type	Screw	
	tool	PZ2	
<hr/>			
Weight		g	50



Wiring diagrams

Certifications and compliance

Certificates

ETIM classification

EC000066 - Power contactor, AC switching