



Product data sheet

Power tools for trade & industry

HWS 88/230

INDUSTRIAL HWS 88/230

For medium-duty to heavy-duty grinding work

The most important data

Permitted sanding disc diameter	230 mm
No-load speed	6,600 rpm
Rated power, output	1,500 W

Part Number 0 602 332 534



Technical data

Technical data

Frequency	300 Hz
Voltage	200 V
Permitted sanding disc diameter	230 mm
No-load speed	6,600 rpm
Rated power, input	2,900 W
Rated power, output	1,500 W
Rated current	10 A
Weight as per EPTA	7.1 kg
Toolholder, drive end	M14
Switch version	Safety switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

