

10177

Wall Bracket 1-3 Products, 160 mm, Orange



Storage of cleaning equipment ensures good hygiene practice and extends the shelf life of equipment. Fully colour coded, you can extend the bracket by adding one more next to the first bracket. You can mix rubber clips and hooks. Easy to clean, by removing the hooks and rubber clips they can be cleaned in an autoclave. The rubber clip can hold products with Ø25-35 mm.

Technical Data

Item Number	10177
Holds products between	25 - 34 mm
Material	Polypropylene TPE Rubber
Suitable for Food Contact (EU 1935/2004), ¹	No
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Box Quantity	5 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	1140 Pcs.
Quantity Per Layer (Pallet)	60 Pcs.
Box Length	330 mm
Box Width	175 mm
Box Height	95 mm
Length	160 mm
Width	80 mm
Height	60 mm
Gross Weight	0,163 kg
Net Weight	0,14 kg
Cubik metre	0,0008 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max usage temperature (non food contact)	80 °C
Min. usage temperature	-10 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020101779
GTIN-14 Number (Box quantity)	15705020101776
Commodity Code	39241000
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.