

FR28 - Flame Resistant Light Weight Anti-Static Coverall 280g

Collection: Bizflame™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre

Outer Carton: 12

Product information

Constructed using a lighter weight highly innovative flame resistant BizFlame Plus fabric.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards. Triple stitching and brass zips throughout for extra strength and durability.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

EN 17353 Type B2 (TESTING IN PROGRESS)



Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Side access openings
- Sleeve pocket
- Two tier knee pad pockets allowing two positioning options
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access

PORTWEST®



FR28 - Flame Resistant Light Weight Anti-Static Coverall 280g

Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/13017-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR28BKRS	Black	43.0	28.0	46.0	1.3400	0.0554	5036108283958	15036108774149
FR28BKRM	Black	43.0	28.0	46.0	1.3700	0.0554	5036108283941	15036108774132
FR28BKRL	Black	43.0	28.0	46.0	1.4000	0.0554	5036108283934	15036108774125
FR28BKRXL	Black	43.0	28.0	46.0	1.4800	0.0554	5036108283965	15036108774156
FR28BKRXXL	Black	43.0	28.0	46.0	1.4600	0.0554	5036108283972	15036108774163