

Features

- Power usage indicator
- 230 – 250V
- Displays wattage, voltage, current, frequency and cost
- 7 programmable functions
- Type E plug (FR)
- Domestic and industrial use

RS PRO Power Metering Socket French Plug (Type E)

RS Stock No.: 178-5376



RS PRO is the own brand of RS, offering professional quality products and solutions across all industries and technologies. Our product range is rigorously tested, inspected, and audited against demanding international standards to provide you with industrial-grade quality, at the right price. Making RS PRO your smart choice.

Product Description

A power meter with a 2 Pin Type E French plug and socket for monitoring and testing instruments and devices to determine the energy consumption and electricity cost.

General Specifications

Type	Power Meter
Input	Type E Socket (French)
Properties Measure	Voltage (V), Wattage (W), Current (A), Frequency (Hz), Cost (KWH)

Display Range

Parameter	Range
Timing	0 second - 9999 days
Wattage	0W - 9999W
Voltage	0V - 9999V
Current	0.000A -16.000A
Frequency	0Hz---9999Hz
Kilowatts Per Hour Cost	0.00 COST/KWH - 99.99COST/KWH

Electrical Specifications

Power Source	Mains
Plug Type	Type E French Plug
Operating Voltage	230V
Voltage Range	230 – 250V
Operating Current	16A max
Frequency	50Hz

Mechanical Specifications

Length	3in
--------	-----

Approvals

Compliance/Certifications	CE
---------------------------	----